



High-precision aluminium spirit level Highprecision R1000, Length: 2000mm



Order data

Order number	467460 2000
GTIN	4007368101109
Item class	46M

Description

Version:

Extremely sturdy 4-chamber profile with shock-absorbing rubber end caps. Flush-mounted horizontal vial for undistorted view of the bubble. If the alignment is not level, the vial bubble travel is **5x greater than for conventional spirit levels**. Out-of-true alignments can thus be noticed more quickly, this enables **quick and highly precise alignment of surfaces**.

Technical description

Length	2000 mm
Error limit in normal position	0.3 mm/m
Type of product	Spirit level