

PLANOLITH**Test frame 90°, rectangular shape accuracy 00, Length×Width: 350X250mm**

Order data

Order number	431730 350X250
GTIN	2050001039163
Item class	46H

Description

Version:

For material, accuracy standards and options see No. 430300; 430400. The four all-round narrow 90° surfaces of the square are precision diamond lapped to DIN 876. Right angle tolerances to DIN 875.

Application:

For checking 90° angles in horizontal and vertical planes.

Supplied with:

Transport packaging

Note:

Delivery excluded. Granite reference squares in square shape up to 1000 mm on request. Granite reference squares in rectangular shape up to 2000 mm on request.

Wooden box or flight case available on request at an additional charge.

Technical description

Width	250 mm
Thickness	50 mm
Length	350 mm
Weight	8 kg
Right angle tolerance	0.002 mm
Standard	DIN 875

Standard	DIN 876/00
Test certificate	Manufacturer's test certificate
Type of product	Graduated plate