

PLANOLITH**Guide and clamping T-slot rail including installation, for plate length: 800mm****Order data**

Order number	431700 800
GTIN	2050001039095
Item class	46H

Description**Version:**

Made of special low-torsion steel, glare-free satin chrome-plated surface, bonded to the granite plate so that it cannot move.

Accuracy:

0.01 mm / 1000 mm, version B. With tenon and T-slot, ground. The nominal dimension 14 mm is only approximate, accessories such as tailstocks etc. need to be ground precisely to the actual slot pitch.

Note:

When ordering, please specify the position of the T-slot rail in the surface and take into account the minimum thickness of the granite plate. Prices for intersecting and end face T-slots on request.

Technical description

for plate length	800 mm
Minimum thickness of granite plate	100 mm
Type of product	Guide rail