

STABILA **Light metal spirit level R-profile, Length: 800 mm****Order data**

Order number	467405 800
GTIN	4005069183721
Item class	46M

Description**Version:**

Distortion-free aluminium R-profile for the most demanding applications.

- **High security against tipping over during measurement due to the extra-wide measuring face (4 cm).**
- **Marking out / cutting along the full profile length without removal due to reliable guidance from the three scribing edges. Continuous frame element across the horizontal vial.**
- **Handgrip with full-length finger groove.**
- **Removable and shock-damping end caps with patented anti-slip stoppers. With two coated measuring faces, two vertical vials and one horizontal vial.**

Error limit in normal position: 0.5 mm/m

Error limit for overhead measurement: 0.5 mm/m

Technical description

Length	800 mm
Error limit in normal position	0.5 mm/m
Error limit for overhead measurement	0.5 mm/m
Type of product	Spirit level