

**High-precision aluminium spirit level Highprecision R1000, Length: 1000mm****Order data**

Order number	467460 1000
GTIN	4007368101062
Item class	46M

**Description****Version:**

Extremely sturdy 4-chamber profile with shock-absorbing rubber end caps. Flush-mounted horizontal vial for undistorted view of the bubble. If the alignment is not level, the vial bubble travel is **5× greater than for conventional spirit levels**. Out-of-true alignments can thus be noticed more quickly, this enables **quick and highly precise alignment of surfaces**.

**Technical description**

Length	1000 mm
Error limit in normal position	0.3 mm/m
Type of product	Spirit level