



Winkeltronic protractor, resolution 0.1 degrees, Length: 400mm



Order data

Order number	467540 400
GTIN	4016054102320
Item class	46R

Description

Version:

Protractor with precise display of the angular position of the movable blade. With integral horizontal and vertical vials. Data storage key for locking the measurement values. Display can be zeroed in any position.

Supplied with:

4 batteries No. 081561 size LR6, case.

Technical description

Graduations	0.1 degrees
Length	400 mm
Measuring range	0 - 200 degrees
Number of batteries contained	4
Article no of the battery / rechargeable battery fitted	081561 LR6
Error limit	0.2 degrees
Power supply	Battery-powered

Calibration	H2
Measurement technology	digital
Type of product	Spirit level

Services

Calibration Engineer's level / electronic clinometer Accuracy 0,10 mm/m	026620 0,10
--	-------------

Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
---	------------