



## High-precision aluminium spirit level Highprecision R1000, Length: 1200mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 467460 1200   |
| GTIN         | 4007368101086 |
| Item class   | 46M           |

### Description

#### Version:

Extremely sturdy 4-chamber profile with shock-absorbing rubber end caps. Flush-mounted horizontal vial for undistorted view of the bubble. If the alignment is not level, the vial bubble travel is **5x greater than for conventional spirit levels**. Out-of-true alignments can thus be noticed more quickly, this enables **quick and highly precise alignment of surfaces**.

### Technical description

|                                |              |
|--------------------------------|--------------|
| Length                         | 1200 mm      |
| Error limit in normal position | 0.3 mm/m     |
| Type of product                | Spirit level |