



## Digital caliper with large display, Measuring range: 150mm



### Order data

Order number	412717 150
GTIN	4059192002107
Item class	43A

### Description

#### Version:

Easy-to-read, high-contrast LCD display with 11 mm high characters. Modern energy-efficient measuring system, operational life approx. 3 years. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons. Lapped slides, the measuring faces are precision lapped. With square depth gauge.

#### Supplied with:

1 battery No. 081560 size CR2032

### Technical description

Jaw length	40 mm
Digit height LCD display	11 mm
Standard	ISO 13385
Depth gauge available	yes
Calibration	A1
Working time	approx. 3 years
Reversible reading	mm / inch
Depth gauge	rectangular 3.7×1.3
Scale divisions	0.01 mm
Scale divisions	0.0005 in

Measuring range	0 - 150 mm
Measured value saving	MAHR reference-lock system
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Power supply	Battery-powered
Measurement deviation E MPE	$\pm 0.03$ mm
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

## Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

## Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---------------------------------------------------	---------------