

Mitutoyo
Digital Solar caliper, Measuring range: 150 mm

Order data

Order number	412650 150
GTIN	4946368212616
Item class	44A

Description
Version:

Measured result is displayed in easy-to-read characters (height 9 mm). The capacitive measuring system is protected against dust and against water damage to the measuring beam, absolute system.

- **Absolute scale, no zeroing necessary, resulting in faster, more reliable measuring.**
- **Low power consumption (20,000 hours continuous use), battery charge indicator**

Supplied with:

With **solar cells** instead of a battery; only low lighting required (60 Lux).

Packaging: sturdy box

Standard: DIN 862

Depth gauge: flat

Measured value saving: Once-off setting of the zero position

Calibration: A1

Scale divisions: 0.01 mm

Error limit: 0.03 mm

Jaw length: 40 mm

Technical description

Jaw length	40 mm
Solar cells	yes
Digit height LCD display	9 mm
Depth gauge	flat
Calibration	A1

Depth gauge available	yes
Standard	DIN 862
Scale divisions	0.01 mm
Error limit	0.03 mm
Measuring range	0 - 150 mm
Measured value saving	Once-off setting of the zero position
Power supply	solar-powered
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Vernier caliper standard

Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	011030 200
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	011050 200

Accessories

Plastic case Type MS150	412468 MS150
Plastic case Type MS150	412470 MS150
Depth gauge holder, metal with 2 screws	412120