

Mitutoyo

Digital Solar caliper, Measuring range: 200 mm



Order data

Order number	412650 200
GTIN	4946368212623
Item class	44A

Description

Version:

Measured result is displayed in easy-to-read characters (height 9 mm). The capacitive measuring system is protected against dust and against water damage to the measuring beam, absolute system.

- **Absolute scale, no zeroing necessary, resulting in faster, more reliable measuring.**
- **Low power consumption (20,000 hours continuous use), battery charge indicator**

Supplied with:

With **solar cells** instead of a battery; only low lighting required (60 Lux).

Packaging: sturdy box

Standard: DIN 862

Depth gauge: flat

Measured value saving: Once-off setting of the zero position

Calibration: A1

Scale divisions: 0.01 mm

Error limit: 0.03 mm

Jaw length: 50 mm

Technical description

Standard	DIN 862
Depth gauge available	yes
Solar cells	yes
Depth gauge	flat
Jaw length	50 mm

Calibration	A1
Digit height LCD display	9 mm
Scale divisions	0.01 mm
Error limit	0.03 mm
Measuring range	0 - 200 mm
Measured value saving	Once-off setting of the zero position
Power supply	solar-powered
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Vernier caliper standard

Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	011030 200
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	011050 200

Accessories

Depth gauge holder, metal with 2 screws	412120
---	--------