

Mahr**Digital caliper with rod type depth gauge and data output, Measuring range: 150mm****Order data**

Order number	412728 150
GTIN	4059192002121
Item class	43A

Description**Version:**

Easy-to-read, high-contrast LCD display with 8.5 mm high characters. Modern energy-efficient measuring system, operational life approx. 3 years. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons. Lapped slides, the measuring faces are precision lapped.

Supplied with:

1 battery No. 081560 size CR2032

Optional extras:

Data cable No. 498940.

Technical description

Standard	ISO 13385
Digit height LCD display	8.5 mm
Calibration	A1
Depth gauge available	yes
Depth gauge	Ø 1.6
Jaw length	40 mm

Reversible reading	mm / inch
Working time	approx. 3 years
Scale divisions	0.01 mm
Scale divisions	0.0005 in
Measuring range	0 - 150 mm
Measured value saving	MAHR reference-lock system
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Power supply	Battery-powered
Measurement deviation E MPE	±0.03 mm
Interface	RS232C interface
Interface	USB interface
Interface	Digimatic interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200

Accessories

Receiver / USB keyboard interface Type	498965
Button cell / special battery Battery type CR2032	081560 CR2032
Connection cablesimplex with data key Type USB2	498940 USB2

Connection cablesimplex with data key Type R2	498940 R2
Multi-receiver / USB keyboard interface Type	498975
Transmitter Type S4E	498966 S4E
Connection cablesimplex with data key Type D2	498940 D2