

Mitutoyo
Digital caliper with AOS system, Measuring range: 150mm

Order data

Order number	412632 150
GTIN	4946368667720
Item class	44A

Description
Version:

Measured result is displayed in easy-to-read characters (height 9 mm). The **AOS (Advanced Onsite Sensor)** electromagnetic measurement system offers enhanced protection against water and dust.

- **Absolute scale, no zeroing necessary, resulting in faster, more reliable measuring.**
- **Low power consumption (20,000 hours continuous use), battery charge indicator**

Supplied with:

1 battery No. 081560 size 357.

Optional extras:

Battery compartment cover No. 412239 size B.

Technical description

Standard	ISO 13385
Depth gauge	rectangular 3.7×1.4
Calibration	A1
Digit height LCD display	9 mm
Depth gauge available	yes
Working time	20000 h
Jaw length	40 mm
Scale divisions	0.01 mm
Measuring range	0 - 150 mm

Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1
Power supply	Battery-powered
Measurement deviation E MPE	±0.02 mm
Measurement method of the measuring instrument	electro-magnetic inductive procedure
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200

Accessories

Depth gauge holder, metal with 2 screws	412120
Button cell / special battery Battery type 357	081560 357
Battery compartment cover Type B	412239 B