

**Mitutoyo****Digital caliper IP67 solar, Measuring range: 150 mm****Order data**

Order number	412655 150
GTIN	4946368532899
Item class	44A

**Description****Version:**

Electronic caliper with absolute electronics and large easy-to-read display. Resistant to water, oil, and dust. Low energy consumption permits 18000 h continuous use on a single battery (size 300: 5000 h). The device is turned on automatically when it is moved and switches off automatically when not used for about 20 minutes.

With solar cells, without battery; only low lighting necessary (from 60 Lux).

**Function:**

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Packaging: sturdy box

Standard: DIN 862

Depth gauge: flat

IP Index of Protection: IP 67

Measured value saving: Once-off setting of the zero position

Calibration: A1

Scale divisions: 0.01 mm

Error limit: 0.03 mm

Jaw length: 40 mm

**Technical description**

Depth gauge available	yes
Auto switch-off	yes
Depth gauge	flat

Solar cells	yes
Calibration	A1
Jaw length	40 mm
Standard	DIN 862
Scale divisions	0.01 mm
Error limit	0.03 mm
Measuring range	0 - 150 mm
Measured value saving	Once-off setting of the zero position
IP Index of Protection	IP 67
Power supply	solar-powered
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Vernier caliper standard

## Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	011030 200
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	011050 200

## Accessories

Depth gauge holder, metal with 2 screws	412120
---	--------