



Dial calipers, Type: 150/01



Order data

Order number	412350 150/01
GTIN	4045197203083
Item class	41Z

Description

Version:

Satin chrome-plated scale. Shock-proof, with protected rack. Precision dial indicator with rotating dial and locking screw. Readings of 1 mm on the beam, 1/100 mm on the round dial.

Thread table: Calipers table

Calibration: A1

Measuring range: 0 - 150 mm

Reading (round dial): 0.01 mm

Pointer revolution: 1 mm

Jaw length: 40 mm

Technical description

Calibration	A1
Pointer revolution	1 mm
Measuring range	0 - 150 mm
Jaw length	40 mm
Reading (round dial)	0.01 mm
Standard	DIN 862
Depth gauge	flat
Measurement technology	analogue
Material	Stainless steel, INOX

all parts	hardened
Packaging	sturdy box
Thread table	Calipers table
Type of product	Dial calipers

Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	011030 200
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	011050 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Plastic case Type MS150	412470 MS150
Plastic case Type MS150	412468 MS150
Table for calipers	412180