



## Digital caliper with data output, Measuring range: 150mm



### Order data

Order number	412729 150
GTIN	4059192002145
Item class	43A

### Description

#### Version:

Easy-to-read, high-contrast LCD display with 8.5 mm high characters. Modern energy-efficient measuring system, operational life approx. 3 years. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons. Lapped slides, the measuring faces are precision lapped.

#### Supplied with:

1 battery No. 081560 size CR2032

#### Optional extras:

Data cable No. 498940.

### Technical description

Reversible reading	mm / inch
Depth gauge	rectangular 3.7×1.3
Calibration	A1
Digit height LCD display	8.5 mm
Standard	ISO 13385
Working time	approx. 3 years
Depth gauge available	yes
Jaw length	40 mm

Scale divisions	0.01 mm
Scale divisions	0.0005 in
Measuring range	0 - 150 mm
Measured value saving	MAHR reference-lock system
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Measurement deviation E MPE	± 0.03 mm
Interface	RS232C interface
Interface	USB interface
Interface	Digimatic interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

## Services

DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200

## Accessories

Connection cables simplex with data key Type R2	498940 R2
Transmitter Type S4E	498966 S4E
Connection cables simplex with data key Type USB2	498940 USB2
Button cell / special battery Battery type CR2032	081560 CR2032
Connection cables simplex with data key Type D2	498940 D2

Multi-receiver / USB keyboard interface Type	498975
Receiver / USB keyboard interface Type	498965