

**Mitutoyo**
**Digital caliper with AOS system, Measuring range: 200mm**

**Order data**

Order number	412632 200
GTIN	4946368667737
Item class	44A

**Description**
**Version:**

Measured result is displayed in easy-to-read characters (height 9 mm). The **AOS (Advanced Onsite Sensor)** electromagnetic measurement system offers enhanced protection against water and dust.

- **Absolute scale, no zeroing necessary, resulting in faster, more reliable measuring.**
- **Low power consumption (20,000 hours continuous use), battery charge indicator**

**Supplied with:**

1 battery No. 081560 size 357.

**Optional extras:**

Battery compartment cover No. 412239 size B.

**Technical description**

Standard	ISO 13385
Depth gauge	rectangular 3.7×1.4
Calibration	A1
Working time	20000 h
Jaw length	50 mm
Depth gauge available	yes
Digit height LCD display	9 mm
Scale divisions	0.01 mm
Measuring range	0 - 200 mm

Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1
Power supply	Battery-powered
Measurement deviation E MPE	±0.02 mm
Measurement method of the measuring instrument	electro-magnetic inductive procedure
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

## Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

## Accessories

Button cell / special battery Battery type 357	081560 357
Depth gauge holder, metal with 2 screws	412120
Battery compartment cover Type B	412239 B