



Digital caliper with data output, Measuring range: 200 mm



Order data

Order number	412729 200
GTIN	4059192002169
Item class	43A

Description

Version:

Easy-to-read, high-contrast LCD display with 8.5 mm high characters. Modern energy-efficient measurement system, operational life approx. 3 years. The reference-lock function prevents measurement errors arising from accidentally touching the control buttons. Lapped slides, the measuring faces are precision lapped.

Supplied with:

1 battery No. 081560 size CR2032

Optional extras:

Data cable No. 498940.

Packaging: sturdy box

Standard: DIN 862

Reversible reading: mm / inch

Depth gauge: flat

Measured value saving: MAHR reference-lock system

Calibration: A1

Scale divisions: 0.01 mm

Scale divisions: 0.0005 in

Error limit: 0.03 mm

Jaw length: 50 mm

Technical description

Reversible reading	mm / inch
Depth gauge available	yes
Depth gauge	flat

Standard	DIN 862
Calibration	A1
Jaw length	50 mm
Working time	approx. 3 years
Digit height LCD display	8.5 mm
Scale divisions	0.01 mm
Scale divisions	0.0005 in
Error limit	0.03 mm
Measuring range	0 - 200 mm
Measured value saving	MAHR reference-lock system
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Power supply	Battery-powered

Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	011030 200
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	011050 200
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200

Accessories

Receiver / USB keyboard interface Type	498965
Transmitter Type S4E	498966 S4E
Button cell / special battery Battery type CR2032	081560 CR2032
Connecting cable Type USB2	498940 USB2

Connecting cable Type D2	498940 D2
Connecting cable Type R2	498940 R2
Multi-receiver / USB keyboard interface Type	498975