

**TESA****Dial calipers, Type: 150/02****Order data**

Order number	412416 150/02
GTIN	7630041105353
Item class	45A

**Description****Version:**

Satin chrome-plated scale. Shock-proof, with protected rack. Precision dial indicator with rotating dial and locking screw.

Especially slim depth gauge. Readings of 1 mm on the beam, 2/100 mm on the round dial.

**Optional extras:**

Thread table No. 412180 for caliper back.

**Technical description**

Calibration	A1
Pointer revolution	2 mm
Measuring range	0 - 150 mm
Reading (round dial)	0.02 mm
Jaw length	40 mm
Measurement deviation E MPE	±0.03 mm
Standard	ISO 13385
Depth gauge	rectangular 3.6×1.7
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened

Packaging	sturdy box
Type of product	Dial calipers

**Services**

DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200