

 Mahr**Digital caliper with large display and rod type depth gauge, Measuring range: 150mm****Order data**

Order number	412716 150
GTIN	4059192002084
Item class	43A

Description**Version:**

Easy-to-read, high-contrast LCD display with 11 mm high characters. Modern energy-efficient measuring system, operational life approx. 3 years. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons. Lapped slides, the measuring faces are precision lapped. With rod type depth gauge.

Supplied with:

1 battery No. 081560 size CR2032

Technical description

Depth gauge available	yes
Depth gauge	Ø 1.6
Digit height LCD display	11 mm
Working time	approx. 3 years
Standard	ISO 13385
Reversible reading	mm / inch
Calibration	A1
Jaw length	40 mm
Scale divisions	0.01 mm

Scale divisions	0.0005 in
Measuring range	0 - 150 mm
Measured value saving	MAHR reference-lock system
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Measurement deviation E MPE	± 0.03 mm
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200
CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------