

Garant
Chamfer mill 60°, Weldon shank, Type: 5

Order data

Order number	216552 5
GTIN	4045197851734
Item class	210

Description
Note:

Use GARANT torque screwdriver TQ No. **211750 size 1.2** with bit No. **674252 size 8IP**.

Technical description

Overall length L_{tot}	70 mm
maximum chamfering $\varnothing D_{max}$	16 mm
Shank $\varnothing D_s$ h6	12 mm
suitable indexable insert	260982 HB725-1
Insert screw	219795 1 (8IP; 1.2 Nm)
Overhang L_1	20 mm
Number of cutting edges Z	1
$\varnothing D$	5.4 mm
Shank type	Weldon shank
Chamfering angle forwards	60 degrees
Through-coolant	yes
Tool exchange	PowerCard
Type of product	Indexable end mill

Accessories

Clamping screw Type 1	219795 1
Torque screwdriver, fixed setting set torque 1,2 N·m	211750 1,2
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
