

**Tipper truck RAL 7016 with discharge valve, Skip volume: 250l**

Order data

| | |
|--------------|---------------|
| Order number | 919923 250 |
| GTIN | 4017976247014 |
| Item class | 96D |

Description**Version:**

Oil-tight welded skip, on bearings for tipping.

Skip edge folded over twice at the top.

Chassis with integral fork lift slots, standing area and tilt lock.

2 fixed wheels and 2 castors (with parking brake) with TPE tyres, hubs with grooved ball bearings.

TOTALSTOP - central braking system to EN 1757-3 fitted as standard to the castors.

Callout:

Discharge valve

with sieve for separating liquids from solids.

Tipping action is operated manually.

For emptying using a forklift truck or when heavily loaded we recommend a self-tipper.

Standard:

EN 1757-3

Colour:

Anthracite RAL 7016 **powder-coated.**

Technical description

| | |
|--------------------------------------|--------------------|
| Height | 780 mm |
| Wheel Ø | 200 mm |
| Filling edge height with rollers | 780 mm |
| Bucket height | 413 mm |
| Internal dimension at intake: height | 72 mm |
| Width | 713 mm |
| Internal dimension at intake: width | 194 mm |
| Bucket length | 1200 mm |
| Skip volume | 250 l |
| Safe working load | 750 kg |
| Bucket width | 652 mm |
| Length | 1359 mm |
| Weight | 70 kg |
| Fork-lift fork socket pitch B | 203 mm |
| Type of product | Tilting containers |