

**Tipper truck RAL 7016 with discharge valve, Skip volume: 600l**

Order data

Order number	919923 600
GTIN	4017976247038
Item class	96D

Description**Version:**

Oil-tight welded skip, on bearings for tipping.

Skip edge folded over twice at the top.

Chassis with integral fork lift slots, standing area and tilt lock.

2 fixed wheels and 2 castors (with parking brake) with TPE tyres, hubs with grooved ball bearings.

TOTALSTOP - central braking system to EN 1757-3 fitted as standard to the castors.

Callout:

Discharge valve

with sieve for separating liquids from solids.

Tipping action is operated manually.

For emptying using a forklift truck or when heavily loaded we recommend a self-tipper.

Standard:

EN 1757-3

Colour:

Anthracite RAL 7016 **powder-coated.**

Technical description

Weight	95 kg
Safe working load	750 kg
Wheel Ø	200 mm
Internal dimension at intake: height	72 mm
Height	1099 mm
Bucket length	1321 mm
Skip volume	600 l
Bucket height	735 mm
Length	1458 mm
Internal dimension at intake: width	194 mm
Filling edge height with rollers	843 mm
Fork-lift fork socket pitch B	327 mm
Bucket width	794 mm
Width	855 mm
Type of product	Tilting containers