

Burr Z7 - medium, diamond cut, Carbide, Type: D1614



Order data

Order number	540200 D1614
GTIN	4045197155016
Item class	51D

Description

Version:

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Ball shape** (KUD)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: ball

Head Ø: 16 mm

Head length L₁: 14 mm Overall length: 54 mm

Shank Ø: 6 mm

Technical description

Shape	D1614
Type of cut	staggered teeth
Tooth type abbreviation	Z7
Head length L ₁	14 mm
Toothing grit designation	medium
Overall length	54 mm

Shape description	ball
Shank Ø	6 mm
Head ∅	16 mm
Tool material	Carbide
Type of product	Burr