

# Burr, coated Z7 – medium, diamond cut, Carbide TiAlN, Type: AS1225



## **Order data**

Order number	540260 AS1225
GTIN	4027497036264
Item class	56L

## **Description**

#### **Version:**

Shank Ø 6 mm.

LUKAS burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge stability, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Additional TiAIN coating for longer working life and temperature resistance.

For high thermal and mechanical loadings (Heavy Duty). **Cylindrical shape AS** (ZYAS), **with end cut.** 

## **Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: Cylindrical with end cut

Head Ø: 12 mm

Head length L₁: 25 mm Overall length: 65 mm

Shank Ø: 6 mm

# **Technical description**

Tooth type abbreviation	Z7
Head length L <sub>1</sub>	25 mm
Shape	AS1225
Type of cut	staggered teeth

Shape description	Cylindrical with end cut
Toothing grit designation	medium
Overall length	65 mm
Head ∅	12 mm
Shank Ø	6 mm
Tool material	Carbide TiAIN
Coating	TiAlN
Type of product	Burr