

Garant

Burr Z7 – medium, diamond cut, Carbide, Type: C0820



Order data

Order number	540200 C0820
GTIN	4045197154934
Item class	51D

Description

Version:

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Cylindrical ball nose shape** (WRC)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: ball nose

Head Ø: 8 mm

Head length L₁: 20 mm

Overall length: 60 mm

Shank Ø: 6 mm

Technical description

Tooth type abbreviation	Z7
Type of cut	staggered teeth
Shape	C0820
Overall length	60 mm
Toothing grit designation	medium
Shape description	ball nose

Head Ø	8 mm
Head length L ₁	20 mm
Shank Ø	6 mm
Tool material	Carbide
Type of product	Burr