

Garant

Burr Z7 – medium, diamond cut, Carbide, Type: G1020



Order data

Order number	540200 G1020
GTIN	4045197155030
Item class	51D

Description

Version:

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Gothic arch shape** (SPG).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: pointed

Head Ø: 10 mm

Head length L₁: 20 mm

Overall length: 60 mm

Shank Ø: 6 mm

Technical description

Shape	G1020
Toothing grit designation	medium
Type of cut	staggered teeth
Head Ø	10 mm
Tooth type abbreviation	Z7
Overall length	60 mm

Shape description	pointed
Head length L ₁	20 mm
Shank Ø	6 mm
Tool material	Carbide
Type of product	Burr