



## Diamond riffler file, 150 mm Grit D126 (medium) general-purpose, Type: 1L



### Order data

Order number	529650 1L
GTIN	4007220016978
Item class	53B

### Description

#### Version:

Shape similar to No. 528050, but covered at both ends with diamond powder of uniform grit.

#### Application:

For precision finishing of form tools made of **hardened steel** or **carbide**.

#### Minimum pressure in use.

### Technical description

Cross-section with coating	3.8×1.6 mm
Shape description	flat plain, straight
Coating length	25 mm
Grinding media	Diamond
Grinding medium code	D
Grit	D126
Overall length	150 mm
Type of product	Riffler file

### User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		

Steel < 60 HRC	suitable
Steel < 67 HRC	suitable
Carbide (HM)	suitable
INOX	suitable
Ti	suitable
GG(G)	suitable
Plastic, GRP	suitable
Stone	suitable only under restricted conditions