

## Garant

### Burr Z7 – medium, diamond cut, Carbide, Type: G1225



#### Order data

Order number	540200 G1225
GTIN	4045197155054
Item class	51D

#### Description

##### Version:

Shank Ø 6 mm.

**GARANT** burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Gothic arch shape** (SPG).

##### Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: pointed

Head Ø: 12 mm

Head length L<sub>1</sub>: 25 mm

Overall length: 65 mm

Shank Ø: 6 mm

#### Technical description

Tooth type abbreviation	Z7
Type of cut	staggered teeth
Overall length	65 mm
Head length L <sub>1</sub>	25 mm
Head Ø	12 mm
Shape	G1225

Shape description	pointed
Toothing grit designation	medium
Shank Ø	6 mm
Tool material	Carbide
Type of product	Burr