

Garant

Burr Z7 – medium, diamond cut, Carbide, Type: G1630



Order data

Order number	540200 G1630
GTIN	4045197155078
Item class	51D

Description

Version:

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Gothic arch shape** (SPG).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: pointed

Head Ø: 16 mm

Head length L₁: 30 mm

Overall length: 70 mm

Shank Ø: 6 mm

Technical description

Head Ø	16 mm
Tooth type abbreviation	Z7
Toothing grit designation	medium
Head length L ₁	30 mm
Shape	G1630
Shape description	pointed

Overall length	70 mm
Type of cut	staggered teeth
Shank Ø	6 mm
Tool material	Carbide
Type of product	Burr