

# Burr Z7 – medium, diamond cut, Carbide, Type: C1625



### **Order data**

Order number	540200 C1625
GTIN	4045197154965
Item class	51D

## **Description**

#### **Version:**

Shank Ø 6 mm.

**GARANT** burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Cylindrical ball nose shape** (WRC)

### **Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: ball nose

Head Ø: 16 mm

Head length L<sub>1</sub>: 25 mm Overall length: 65 mm

Shank Ø: 6 mm

## **Technical description**

Tooth type abbreviation	<b>Z</b> 7
Toothing grit designation	medium
Head length L <sub>1</sub>	25 mm
Head ∅	16 mm
Overall length	65 mm
Type of cut	staggered teeth

Shape description	ball nose
Shape	C1625
Shank Ø	6 mm
Tool material	Carbide
Type of product	Burr