

Garant
Burr Z7 – medium, diamond cut, Carbide, Type: D0605

Order data

Order number	540200 D0605
GTIN	4045197154972
Item class	51D

Description
Version:

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Ball shape** (KUD)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: ball

Head Ø: 6 mm

Head length L_1 : 5 mm

Overall length: 50 mm

Shank Ø: 6 mm

Technical description

Type of cut	staggered teeth
Shape description	ball
Toothing grit designation	medium
Shape	D0605
Tooth type abbreviation	Z7
Head Ø	6 mm

Overall length	50 mm
Head length L ₁	5 mm
Shank Ø	6 mm
Tool material	Carbide
Type of product	Burr