

Garant

Burr Z7 – medium, diamond cut, Carbide, Type: AS0820



Order data

Order number	540200 AS0820
GTIN	4045197154880
Item class	51D

Description

Version:

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Cylindrical shape**(ZYAS), **with end cut**.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: Cylindrical with end cut

Head Ø: 8 mm

Head length L₁: 20 mm

Overall length: 60 mm

Shank Ø: 6 mm

Technical description

Tooth type abbreviation	Z7
Type of cut	staggered teeth
Head Ø	8 mm
Head length L ₁	20 mm
Shape	AS0820
Toothing grit designation	medium

Overall length	60 mm
Shape description	Cylindrical with end cut
Shank Ø	6 mm
Tool material	Carbide
Type of product	Burr