

Garant
Burr Z7 – medium, diamond cut, Carbide, Type: F1225

Order data

Order number	540200 F1225
GTIN	4045197155092
Item class	51D

Description
Version:

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Round arch shape** (RBF).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: round arch

Head Ø: 12 mm

 Head length L₁: 25 mm

Overall length: 65 mm

Shank Ø: 6 mm

Technical description

Shape	F1225
Head Ø	12 mm
Shape description	round arch
Head length L ₁	25 mm
Type of cut	staggered teeth
Toothing grit designation	medium

Tooth type abbreviation	Z7
Overall length	65 mm
Shank Ø	6 mm
Tool material	Carbide
Type of product	Burr