

Garant**TCMT 110208, Grade: HB7010-1**

Order data

Order number	260954 HB7010-1
GTIN	4045197852854
Item class	21G

Description

TCMT 110208 HB7010-1 Grade: HB7010-1

Chip breaker: SS

Cutting depth a_p : 0.2 - 1.5 mmFeed f : 0.05 - 0.2 mm/rev.Cutting speed v_c main application: 150 - 500 m/min

Technical description

Cutting depth a_p	0.2 - 1.5 mm
Grade	HB7010-1
Chip breaker	SS
Main application	P
Feed f	0.05 - 0.2 mm/rev.
Cutting conditions	continuous
Cutting speed v_c main application	150 - 500 m/min
Corner radius	0.8 mm

Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	TCMT 110208
Number of changes/inserts	3
Type of product	Indexable insert for turning