

Garant**TCMT 16T308, Grade: HB7020****Order data**

Order number	260958 HB7020
GTIN	4045197852885
Item class	21G

Description

TCMT 16T308 HB7020 Grade: HB7020

Chip breaker: SS

Cutting depth a_p : 0.2 - 1.5 mmFeed f : 0.05 - 0.2 mm/rev.Cutting speed v_c main application: 150 - 400 m/min**Technical description**

Feed f	0.05 - 0.2 mm/rev.
Corner radius	0.8 mm
Chip breaker	SS
Cutting speed v_c main application	150 - 400 m/min
Grade	HB7020
Main application	P
Cutting conditions	slightly interrupted
Cutting depth a_p	0.2 - 1.5 mm

Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	TCMT 16T308
Number of changes/inserts	3
Type of product	Indexable insert for turning