

**Garant****Burr Z5 – fine, Carbide, Type: C1020****Order data**

Order number	540400 C1020
GTIN	4045197155498
Item class	51D

**Description****Version:**

Shank Ø 6 mm.

**GARANT** burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Cylindrical ball nose shape** (WRC)

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

**Technical description**

Overall length	60 mm
Tooth type abbreviation	Z5
Toothing grit designation	fine
Shape description	ball nose
Shape	C1020
Head Ø	10 mm
Shank Ø	6 mm
Head length	20 mm
Series	Tooth configuration Z5
Tool material	Carbide

Type of product

Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		