

### Burr, coated Z7 - medium, diamond cut, Carbide TiAIN, Type: G0618



### **Order data**

Order number	540260 G0618
GTIN	4027497042999
Item class	56L

# **Description**

#### **Version:**

Shank Ø 6 mm.

LUKAS burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge stability, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Additional TiAIN coating for longer working life and temperature resistance.

For high thermal and mechanical loadings (Heavy Duty). **Gothic arch shape** (SPG).

#### **Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: Pointed

Head Ø: 6 mm

Head length L₁: 18 mm Overall length: 50 mm

Shank Ø: 6 mm

## **Technical description**

Toothing grit designation	medium
Head length L₁	18 mm
Shape	G0618
Shape description	Pointed

Overall length	50 mm
Type of cut	staggered teeth
Tooth type abbreviation	Z7
Head ∅	6 mm
Shank Ø	6 mm
Tool material	Carbide TiAIN
Coating	TiAIN
Type of product	Burr