

**Garant****Burr Z5 – fine, Carbide, Type: D1614****Order data**

Order number	540400 D1614
GTIN	4045197155450
Item class	51D

**Description****Version:**

Shank Ø 6 mm.

**GARANT** burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Ball shape** (KUD)

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

**Technical description**

Shape	D1614
Overall length	54 mm
Toothing grit designation	fine
Tooth type abbreviation	Z5
Head Ø	16 mm
Shape description	ball
Shank Ø	6 mm
Head length	14 mm
Series	Tooth configuration Z5

Tool material	Carbide
Type of product	Burr

**User data**

	Suitability	V <sub>c</sub>	ISO code
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		