

Garant
Burr Z FINE – very fine, Carbide, Type: C1225

Order data

Order number	540440 C1225
GTIN	4045197679888
Item class	51D

Description
Version:

 Shank \varnothing 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Cylindrical ball nose shape** (WRC)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Tooth type abbreviation	Z FINE
Overall length	65 mm
Head \varnothing	12 mm
Toothing grit designation	very fine
Shape	C1225
Shape description	Ball nose
Shank \varnothing	6 mm
Head length	25 mm
Series	Tooth configuration Z FINE
Tool material	Carbide

Type of product

Burr

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		