

Setting ring with intermediate sizes, Type: C



Order data

Order number	484035 C
GTIN	4045197212436
Item class	48B

Description

Version:

Setting rings (checking rings) of first class gauge steel, hardened, stress-relieved, ground and lapped. **Each setting ring is engraved with the actual size.** Manufacturer's tolerance for the bore is JS4.

Standard:

Nach **DIN 2250 C.**

Note:

The size designation type describes the nominal dimension in millimetres (mm).

Type A = 3.001 – 3.499

Type B = 3.501 – 14.999

Type C = 15.001 – 19.999

Type D = 20.001 – 24.999

Type E = 25.001 – 31.999

Type F = 32.001 – 39.999

Type G = 40.001 – 49.999

Type H = 50.001 – 59.999

Type I = 60.001 – 69.999

Type J = 70.001 – 79.999

Type K = 80.001 – 89.999

Type L = 90.001 – 99.999

Please state exact nominal \varnothing .

Intermediate size rings are simply setting rings in **fractional sizes!**

For whole number (even) \varnothing see No. 484030 or on request.

Ordering example \varnothing 10.002: No. 484035 B 10.002.

Ceramic setting rings in full millimetre sizes available on request.

Technical description

Tolerance zone	JS
Nominal size	15.001 - 19.999 mm
Standard	DIN 2250 C
Manufacturing tolerance of the bore	JS4
Material	Gauge steel
Quality	4
Calibration	L7
Type of product	setting ring

Services

DAkkS calibrationSetting ring maximum \varnothing 50 mm	028470 50
CalibrationSetting ring maximum \varnothing 50 mm	028400 50