

## Plug gauge "Go" chrome H7, Nominal size Ø: 2mm



### Order data

Order number	484040 2
GTIN	2050001674913
Item class	48B

### Description

#### Version:

The "Go" ends of these working gauges have a **wear allowance** to DIN 7164.

**"Go" end with hard chrome measuring faces.** This increases the gauge life about 8 times.

#### Standard:

Toleranz und Abmaße nach **DIN EN ISO 1938-1, DIN 2245-1 und DIN 7164.**

#### Note:

- **Further intermediate sizes available on request or can simply be ordered at [www.hoffmann-group.com](http://www.hoffmann-group.com), for instance No. 484000 size 82.**

### Technical description

Tolerance zone	H
Standard	DIN 7150-2
Standard	DIN 7164
Quality	7
Nominal size	2 mm
Type of gauge	"Go" plug gauge
Type of gauge	"No Go" gauge
Calibration	M2
Type of product	Pug Gauge

### Services

Calibration "Go" / "No Go" plug gauge maximum $\varnothing$ 20 mm	028300 20
DAkkS calibration "Go" / "No Go" plug gauge maximum $\varnothing$ 60 mm	028340 60