


**HOLEX****Abrasive sleeve (ZA) 80 grit medium, Sleeve Ø×Width of sleeve: 45X30mm****Order data**

Order number	553780 45X30
GTIN	4045197240538
Item class	52E

**Description****Version:**

**The rubber body of the abrasive sleeve holder expands at high speed to hold the abrasive sleeve in place.** The full width of the sleeve can be used, it does not slip and can be replaced quickly and easily (twist in the direction of slots when fitting/removing). Only compatible with abrasive sleeve holders.

Made of non-tearing, synthetic resin bonded material with long service life and good grit adhesion. Unsuitable for use with cooling lubricants.

**Zirconium Aluminium Oxide (ZA).****Application:**

Abrasive sleeves are predominantly used for surface grinding tasks which require the removal of large amounts of material – even at sharp edges.

**Suitable for:**

Abrasive sleeve holder No. 553600.

**Technical description**

Grit	80
Sleeve Ø	45 mm
Sleeve width	30 mm

Grit designation	medium
Grinding media	Zirconium aluminium oxide
Grinding medium code	ZA
Sleeve shape	cylindrical
Type of product	Abrasive sleeve

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
dry	suitable		

### Accessories

Abrasive sleeve holder, slit, shank Ø 6 mm Head Ø×head length 45X30 mm

553600 45X30