

HOLEX®
Tap wrench, adjustable, Type: 4

Order data

Order number	148400 4
GTIN	4045197854995
Item class	12L

Description
Version:

With hardened jaws. Steel handles galvanised. For use in confined spaces one steel handle can be unscrewed.

Standard use:

body made of die-cast zinc.

Norm: DIN 1814

Capacity □: 5.5 - 16 mm

for hand taps DIN 352: M11 – M27

for hand reamer Ø DIN 206: 7 - 20 mm

Overall length: 480 mm

Technical description

Capacity □	5.5 - 16 mm
for hand reamer Ø DIN 206	7 - 20 mm
Overall length	480 mm
for hand taps DIN 352	M11 – M27
Norm	DIN 1814