

**HOLEX®**
**Tap wrench, adjustable, Type: 5**

**Order data**

Order number	148400 5
GTIN	4045197857002
Item class	12L

**Description**
**Version:**

With hardened jaws. Steel handles galvanised. For use in confined spaces one steel handle can be unscrewed.

**Standard use:**

body made of die-cast zinc.

Norm: DIN 1814

Capacity □: 7 - 20 mm

for hand taps DIN 352: M13 – M32

for hand reamer Ø DIN 206: 9 - 26 mm

Overall length: 700 mm

**Technical description**

Capacity □	7 - 20 mm
for hand taps DIN 352	M13 – M32
for hand reamer Ø DIN 206	9 - 26 mm
Overall length	700 mm
Norm	DIN 1814