

HOLEX®
Die stock, for die \varnothing × height: 20X7 mm

Order data

Order number	149300 20X7
GTIN	4045197857033
Item class	12L

Description
Version:

Steel handles galvanised and can be unscrewed. With 5 screws to clamp the die. **Up to size 65×25** of die-cast zinc, **from size 75×20** of steel.

Application:

For direct mounting of solid and adjustable dies to EN 22568.

Norm: EN 22568

Metric thread: M4.5 – M6

Metric fine thread: M5×0.75 – M6×0.75

UNC thread: No.6 – 1/4"

UNF thread: No.8 – 1/4"

Whitworth thread: 3/16" – 1/4"

Overall length: 175 mm

Technical description

Metric fine thread	M5×0.75 – M6×0.75
Height	7 mm
for die \varnothing	20 mm
Overall length	175 mm
Whitworth thread	3/16 – 1/4 inch
Metric thread	M4.5 – M6
UNF thread	No.8 – 1/4 inch
UNC thread	No.6 – 1/4 inch

Norm

EN 22568