

HOLEX®
Die stock, for die \varnothing × height: 25X9 mm

Order data

Order number	149300 25X9
GTIN	4045197857040
Item class	12L

Description
Version:

Steel handles galvanised and can be unscrewed. With 5 screws to clamp the die. **Up to size 65×25** of die-cast zinc, **from size 75×20** of steel.

Application:

For direct mounting of solid and adjustable dies to EN 22568.

Norm: EN 22568

Metric thread: M7 – M9

Metric fine thread: M7×0.5 – M9×1

UNC thread: 5/16"

UNF thread: 5/16"

Whitworth thread: 5/16"

Overall length: 210 mm

Technical description

Metric fine thread	M7×0.5 – M9×1
Height	9 mm
Whitworth thread	5/16 inch
UNC thread	5/16 inch
Metric thread	M7 – M9
for die \varnothing	25 mm
UNF thread	5/16 inch
Overall length	210 mm

Norm

EN 22568