

**HOLEX®**
**Die stock, for die  $\varnothing$  × height: 25,4X9,5 mm**


## Order data

Order number	149300 25,4X9,5
GTIN	4045197857057
Item class	12L

## Description

### Version:

Steel handles galvanised and can be unscrewed. With 5 screws to clamp the die. **Up to size 65×25** of die-cast zinc, **from size 75×20** of steel.

### Application:

For direct mounting of solid and adjustable dies to EN 22568.

Norm: EN 22568

Metric thread: M2 – M12

Metric fine thread: M4 – M10

UNC thread: No.3 – 7/16"

UNF thread: No.3 – 7/16"

Whitworth thread: 5/16" – 1/8"

Whitworth pipe thread: G1/8"

## Technical description

UNF thread	No.3 – 7/16 inch
for die $\varnothing$	25.4 mm
Overall length	210 mm
Metric thread	M2 – M12
Height	9.5 mm
Whitworth pipe thread	G1/8 inch
Whitworth thread	5/16 – 1/8 inch
Metric fine thread	M4 – M10

UNC thread	No.3 – 7/16 inch
Norm	EN 22568