

HOLEX®
Die stock, for die Ø × height: 30X11 mm

Order data

Order number	149300 30X11
GTIN	4045197857064
Item class	12L

Description
Version:

Steel handles galvanised and can be unscrewed. With 5 screws to clamp the die. **Up to size 65×25** of die-cast zinc, **from size 75×20** of steel.

Application:

For direct mounting of solid and adjustable dies to EN 22568.

Norm: EN 22568

Metric thread: M10 – M11

Metric fine thread: M10×0.75 – M11×1

UNC thread: 3/8" – 7/16"

UNF thread: 3/8" – 7/16"

Whitworth thread: 3/8" – 7/16"

Whitworth pipe thread: G1/8"

Technical description

Metric thread	M10 – M11
Overall length	260 mm
UNF thread	3/8 – 7/16 inch
Height	11 mm
UNC thread	3/8 – 7/16 inch
Metric fine thread	M10×0.75 – M11×1
Whitworth thread	3/8 – 7/16 inch
for die Ø	30 mm

Whitworth pipe thread	G1/8 inch
Norm	EN 22568