

HOLEX®
Die stock, for die Ø × height: 38X10 mm

Order data

Order number	149300 38X10
GTIN	4045197857071
Item class	12L

Description
Version:

Steel handles galvanised and can be unscrewed. With 5 screws to clamp the die. **Up to size 65×25** of die-cast zinc, **from size 75×20** of steel.

Application:

For direct mounting of solid and adjustable dies to EN 22568.

Norm: EN 22568

Metric fine thread: M12×1 – M15×1

UNF thread: 1/2" – 9/16"

Whitworth pipe thread: G1/4"

Overall length: 310 mm

Technical description

for die Ø	38 mm
Overall length	310 mm
UNF thread	1/2 – 9/16 inch
Whitworth pipe thread	G1/4 inch
Metric fine thread	M12×1 – M15×1
Height	10 mm
Norm	EN 22568

