

HOLEX®
Die stock, for die \varnothing × height: 38X14 mm

Order data

Order number	149300 38X14
GTIN	4045197857088
Item class	12L

Description
Version:

Steel handles galvanised and can be unscrewed. With 5 screws to clamp the die. **Up to size 65×25** of die-cast zinc, **from size 75×20** of steel.

Application:

For direct mounting of solid and adjustable dies to EN 22568.

Norm: EN 22568

Metric thread: M12 – M14

UNC thread: 1/2" – 9/16"

Whitworth thread: 1/2" – 9/16"

Overall length: 310 mm

Technical description

Metric thread	M12 – M14
Whitworth thread	1/2 – 9/16 inch
Height	14 mm
UNC thread	1/2 – 9/16 inch
for die \varnothing	38 mm
Overall length	310 mm
Norm	EN 22568

